




AIRKOMPRESSOR CLIK TEC 10.0

Manual



CLIK TEC
by SKS GERMANY




Made in Germany

AIRKOMPRESSOR 10.0 › 11661

MAX
10
BAR

MAX
144
PSI



CLIK TEC
by SKS GERMANY

for

SCHWALBE [®]
CLIK VALVE / **CLIK**
VALVE



Incl. conversion set



2 SV-valve inserts



2 DV-valve inserts



1 Valve tool







4 Dust caps

**ONLINE
TUTORIAL**




Valve insert replacement




Exchange gauge floor pumps

**ONLINE
TUTORIAL**




01

Loosen the union nut on the pressure gauge cap



02


Pull up the pressure gauge cap



03


Unscrew the pressure gauge at the bottom
with an Allen key (size 10)

Inbus 10




04

Insert a new pressure gauge
into the pressure gauge holder




05

Screw on the pressure gauge with
a maximum torque of 2 Nm




06

Push the pressure gauge cap down again
and secure it with the union nut




Exchange rubber sealing cuff floor pumps



Remove the two Torx screws (T25) of the hose holder. Pull the cylinder rod out of the tube with a strong jerk.


Remove the old cup seal. If necessary, use a tool to do this (e.g. screwdriver).



03

Place the new cup over the cylinder rod until it is positioned in the designated joint.

CAUTION: Make sure that it is on the correct side!




04

Grease the rubber cup seal, re-insert the cylinder rod and screw it in.


03

Unscrew the pressure gauge at the bottom with an Allen key (size 10).




04

Turn the pressure gauge holder approximately 45° anti-clockwise until you feel resistance. Then pull out the pressure gauge holder.




05

Replace the non-return valve system and follow the steps mentioned above in reverse order.



06

ATTENTION: Please make sure that the non-return valve system is correctly positioned in the designated fixing. Check that the spring is fitted securely!





Warranty policy
sks-germany.com

SKS metaplast Scheffer-Klute GmbH
Zur Hubertushalle 4 | D-59846 Sundern
+49 2933 831-0
service@sks-germany.com